



box of 6 monthly contact lenses

Vision Plus 55

SODIUM HYALURONATE



Unlike other contact lenses already in the market, that are using sodium hyaluronate only in the saline solution where the lenses are immersed, this new lenses special formula let the Sodium Hyaluronate combine with the material of the lens during its hydration and stick to it permanently. In this way, the Sodium Hyaluronate works as a powerful wetting agent all along the wearing cycle not being "released" as a lubricant, but acting continuously to keep the surface of the lens as wet as it should be from the first minute to the last

Advantages

- ✦ Generic white box with private label sticker
- ✦ Available in stock
- ✦ No MOQ required
- ✦ Soft material high wearability
- ✦ The presence of hyaluronic acid linked to the polymer matrix allows prolonged portability and high quality performance throughout the day
- ✦ Better water retention capacity than all hydrogel materials
- ✦ High comfort and effective action against dry eye syndrome
- ✦ Excellent wetting angle

Technical file

Material	Wetafilcon with UV filter
Water content	55%
Geometry	Aspheric
Base curve	8,70 mm
Diameter	14,20 mm
Central thickness	0,08 mm (at -3,00 Dt)
Handling tint	Blue
Power range	-12.00Dt ~ +6.00Dt -12.00 to -6.50 (0.50 step) -6.00 to +4.00 (0.25 step) +4.50 to +6.00 (0.50 step)